

Data Sheet



receiver 26A005

3260 - 2003441
Version:1 03-JUN-2009

Description


Subminiature magnetic receiver (Balanced Armature Type) for use in In The Canal and Completely In the Canal applications with standard response.

Features

- Great ITE, ITC and CIC applications
- High output, maximum peak output 126 dB
- Improved shock performance



Dimensions in mm (inch)




Mechanical Data

Weight	0.17 gr.
Case material	Ni80Fe15Mo5
Solder pad content	Sn96.5Ag3.0Cu0.5
Dimensions	Refer to outline drawing

Typical response curve

Solid curve: Ideal current source 3.32 mA RMS.
Dashed curve: Ideal voltage source 0.17 V RMS.



Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

Data Sheet



receiver 26A005

3260 - 2003441
Version:1 03-JUN-2009

Specifications

Acoustic loading: 10.0 mm of 1.0 mm diameter tubing into a 2 cc coupler.
Constant current drive of 3.32 mA RMS (0.55 mVA @ 1000 Hz).
Environmental conditions: 23 °C (73.4F), 50 % RH

Acoustic parameters		Min	Typ	Max	Unit	Comments
Sensitivity	@ 200 Hz	98.5	101.5	104.5	dB	
	@ 500 Hz	99	102	105	dB	
	@ 1000 Hz	101	104	107	dB	
Peak 1	frequency	2000	2175	2400	Hz	
	output	113.5	116	118	dB	
Valley 1	frequency	3500	4250	5000	Hz	
	output	100	102.5		dB	
Peak 2	frequency	5000	5500	6000	Hz	
	output	104	107	110	dB	
THD	@ 1/3 peak			5	%	
	@ 1/2 peak			5	%	
Maximum output @ peak frequency				126	dB	50 mVA input *

Electric parameters		Min	Typ	Max	Unit	Comments
Impedance @ 1000 Hz		40	50	60	Ohm	
DC resistance @ 20 °C		20	24	28	Ohm	
DC bias current range		zero bias				

Additional parameters		Min	Typ	Max	Unit	Comments
Shock resistance		14000			g	90% survival rate with THD @ 1/2 peak freq. < 10%
Storage temperature range		-40		63	°C	

* Due to low impedance, voltages above 0.447 V can result in rubbing sounds.
A positive voltage applied to the negative terminal (-) will result in an increase in pressure at the sound outlet.

Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible.
Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.