

Data Sheet



receiver 26UA06/7

3260 - 3019267
Version: 2 19-DEC-2008

Description


Subminiature magnetic receiver (Balanced Armature Type) for use in Behind The Ear and In The Ear applications with standard response.
Provided with a mumetal cap for improved robustness and decreased magnetic radiation.



Features

- Excellent for mini BTE, ITE, ITC and CIC applications
- Improved efficiency
- Improved maximum LF output

Dimensions in mm (inch)




Mechanical Data

Weight	0.20 gr.
Case material	Ni80Fe15Mb5
Solder pad content	Sn96.5Ag3.0Cu0.5
Dimensions	Refer to outline drawing

Typical response curve

Refer to specifications section for measurement conditions.



Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible.
Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

Data Sheet



receiver 26UA06/7

3260 - 3019267
Version: 2 19-DEC-2008

Specifications

Acoustic loading: 10.0 mm of 1.0 mm diameter tubing into a 2 cc coupler.
Constant voltage drive of 0.367 V RMS (0.35 mVA @ 500 Hz).
Environmental conditions: 23 °C (73.4F), 50 %RH.

Acoustic parameters		Mn	Typ	Max	Unit	Comments
Sensitivity	@ 200 Hz	103	106	109	dB	
	@ 500 Hz	101	104	107	dB	
	@ 1000 Hz	98.5	101.5	104.5	dB	
Peak 1	frequency	2350	2550	2750	Hz	
	output	104	107	110	dB	
Valley 1	frequency	3600	4350	5100	Hz	
	output	91	94		dB	
Peak 2	frequency	4650	5150	5650	Hz	
	output	94	97	100	dB	
THD	@ 1/3 peak			5	%	
	@ 1/2 peak			5	%	
Maximum output @ peak frequency				126	dB	50 mVA input

Electric parameters		Mn	Typ	Max	Unit	Comments
Impedance @ 1000 Hz		512	640	768	Ohm	
Impedance @ 500 Hz		308	385	462	Ohm	
DC resistance @ 20 °C		211	248	285	Ohm	
DC bias current range		zero bias				

Additional parameters		Mn	Typ	Max	Unit	Comments
Shock resistance		14000			g	90% survival rate with THD @ 1/2 peak freq. < 10%
Storage temperature range		-40		63	°C	

A positive voltage applied to the negative terminal (-) will result in an increase in pressure at the sound outlet.

Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible.
Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.