


## Description

Subminiature magnetic receiver (Balanced Armature Type) for use in In The Canal and Completely In the Canal applications with modified response by means of a damping screen.




## Features

- Great ITE/BTE applications
- High output, maximum peak output 129 dB
- Improved shock performance

## Mechanical data

Weight	0.34 gr.
Case material	Ni80Fe15Mo5
Solder pad material	Sn96.5Ag3.0Cu0.5
Dimensions	Refer to outline drawing

## Product drawing - Dimensions in mm [inch]



Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

## Specifications

Acoustic loading: 10.0 mm of 1.0 mm diameter tubing into a 2 cc coupler.

Constant current drive of 1.08 mA RMS (0.35 mVA @ 1000 Hz).

Environmental conditions: 23°C (73.4F), 50 % RH.

Acoustic parameters		Min	Typ	Max	Unit	Comments
Sensitivity	@ 200 Hz	98.5	101.5	104.5	dB	
	@ 500 Hz	99	102	105	dB	
	@ 1000 Hz	101	104	107	dB	
Peak 1	frequency	1900	2100	2300	Hz	
	output	111	113	114.5	dB	
Valley 1	frequency	3200	3550	3900	Hz	
	output	102.5	105		dB	
Peak 2	frequency	4000	4500	5000	Hz	
	output	104.5	107	109.5	dB	
THD	@ 1/3 peak			5	%	
	@ 1/2 peak			5	%	
Maximum output @ peak frequency				126	dB	@ 50 mVA input power


Electric parameters		Min	Typ	Max	Unit	Comments
Impedance @ 1000 Hz		240	300	360	Ohm	
Impedance @ 500 Hz		136	170	204	Ohm	
DC resistance @ 20°C		85	100	115	Ohm	
DC bias current range		zero bias				

Additional parameters		Min	Typ	Max	Unit	Comments
Shock resistance		14000			g	90% survival rate with THD @ 1/2 peak frequency < 10%
Storage temperature range		-40		63	°C	

A positive voltage applied to the negative terminal (-) will result in an increase in pressure at the sound outlet.

Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

## Typical response curve



Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.